

Quad-Base

ISQB-G 175x175x22

Part no...:10.01.15.00007

<https://www.schmalz.com/10.01.15.00007>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISQB-G 175x175x22

Quad-Base with 2 hose connections, for smooth tables



Dimensions (LxB): 175x175

Basic area: 175 x 175 mm


Length L: 175 mm

Width B: 175 mm

Height H: 22 mm

Hose type: Hose D = 8 d = 6

Design Data



Attribute	Value
B	175 mm
d	60 mm
H	22 mm
L	175 mm

Technical Data

Attribute	Value
Weight	0.99 kg

Accessories

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Quad-Base

ISQB-G 175x175x22

Part no...:10.01.15.00007

<https://www.schmalz.com/10.01.15.00007>



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm

Spare parts

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Quad-Base

ISQB-G 175x175x22

Part no...:10.01.15.00007

<https://www.schmalz.com/10.01.15.00007>



DI-SCHN 8 MOS EPDM-20

Part no...:10.07.04.00002

External diameter D: 8 mm

Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr