

## Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Suction Cups for Vacuum End Effectors > SPB4 40 SI-55 G1/4-AG

### Bellows suction cup (round) for very uneven workpieces



Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/4"-M

Number of folds: 4.5

### Design Data



| Attribute  | Value    |
|------------|----------|
| d2         | 23 mm    |
| dn         | 8 mm     |
| Dmax(S)    | 41.50 mm |
| Ds         | 40.50 mm |
| G1         | G1/4"-M  |
| H          | 73.10 mm |
| LG1        | 10 mm    |
| SW1        | 27 mm    |
| Z (Stroke) | 27 mm    |

### Technical Data

| Attribute                   | Value                 |
|-----------------------------|-----------------------|
| Suction force (-600mbar)    | 25 N                  |
| Pull-off force              | 39 N                  |
| Volume                      | 35.74 cm <sup>3</sup> |
| Hose diameter (rec.) d      | 12 mm                 |
| Number of folds             | 4.50                  |
| Suction cup material        | Silicone SI           |
| Material hardness [Shore A] | 55 Shore A            |
| Size                        | 40                    |

### Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)

## Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

|                |         |
|----------------|---------|
| Weight         | 40.70 g |
| Product family | SPB4    |

### Accessories



#### SIEB 19.5x1 MS-A2 103

Part no...:10.07.01.00321

External diameter D: 19.5 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 103 µm



#### SSB 20-32 ST-VZ

Part no...:10.07.10.00003

Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised



#### SPI 32 PE SPB4-40

Part no...:10.01.06.02856

Size: 32

Material: Polyethylene

Use: SPB4-40

### Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)

## Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>



### SPSE 40

Part no...:10.01.06.02954

Size: 40

## Spare parts



### SC 090 G1/4-AG

Part no...:10.01.06.02793

Connection geometry: 090

Vacuum connection: G1/4"-M

Length L1: 33.5 mm

Fitting length: 7.5 mm

Nominal diameter dn: 8 mm



### SPB4 40 SI-55 SC090

Part no...:10.01.06.02590

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4.5

## Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | [schmalz@schmalz.fr](mailto:schmalz@schmalz.fr)