

Flat suction cup (round)

SGPN 24 NK-40 M5-AG

Part no.:10.01.01.11979

<https://www.schmalz.com/10.01.01.11979>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 24 NK-40 M5-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 24


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Nipple material: Aluminum

Vacuum connection: M5-M

Design Data



Attribute	Value
dn	2.50 mm
Dmax(S)	25.50 mm
Ds	24 mm
G1	M5-M
H	15.80 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	1.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	11 N
Volume	0.85 cm ³
Hose diameter (rec.) d	4 mm
Size	24
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Flat suction cup (round)

SGPN 24 NK-40 M5-AG

Part no.:10.01.01.11979

<https://www.schmalz.com/10.01.01.11979>

Weight	2.10 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016


Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum



SGP 24 NK-40 N016

Part no.:10.01.01.10320

Size: 24

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A