

Bellows suction cup (round)

FG 40 PVC-50 N033

Part no...:10.01.06.02468

<https://www.schmalz.com/10.01.06.02468>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups FG PVC (2.5 Folds) > FG 40 PVC-50 N033

Bellows suction cup (round) for very uneven workpieces




Size: 40

Suction cup material: Polyvinyl chloride PVC

Material hardness [Shore A]: 50 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	10.80 mm
d2	23.40 mm
D1	40.40 mm
Dk	18.70 mm
Dmax(S)	44 mm
Ds	40 mm
H	41.70 mm
H2	20.70 mm
Z (Stroke)	10.90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	21.70 N
Pull-off force	56 N
Volume	15.22 cm ³
Curve radius (min) (convex)	60 mm
Hose diameter (rec.) d	6 mm
Size	40
Nipple family	N 033

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Bellows suction cup (round)

FG 40 PVC-50 N033

Part no.:10.01.06.02468

<https://www.schmalz.com/10.01.06.02468>

Number of folds	2.50
Suction cup material	Polyvinyl chloride PVC
Material hardness [Shore A]	50 Shore A
Weight	14.30 g
Product family	FG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N033 G1/4-AG DN550

Part no.:10.01.01.00818

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N033 G1/4-IG DN550

Part no.:10.01.01.00817

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr