

Bellows suction cups SI-MD (round)

FSGA 14 SI-MD-55 M5-AG

Part no...:10.01.06.04196

<https://www.schmalz.com/10.01.06.04196>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups FSGA SI-MD (1.5 Folds) > FSGA 14 SI-MD-55 M5-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 14

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: M5-M

Number of folds: 1.5

Vacuum connection: M5-M

Design Data



Attribute	Value
d2	5 mm
Dmax(S)	14.50 mm
dn	2.50 mm
Ds	12.50 mm
G1	M5-M
H	20.50 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55 Shore A
Size	14
Number of folds	1.50
Connection	M5-AG
Curve radius (min) (convex)	12.50 mm
Volume	0.42 cm ³

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Bellows suction cups SI-MD (round)

FSGA 14 SI-MD-55 M5-AG

Part no.:10.01.06.04196

<https://www.schmalz.com/10.01.06.04196>

Suction force (-600mbar)	1.20 N
Pull-off force	5 N
Hose diameter (rec.) d	2 mm
Weight	2.10 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SPI 14 PEEK

Part no.:10.01.06.03282

Size: 14

Material: Polyetheretherketon

Spare parts



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Bellows suction cups SI-MD (round)

FSGA 14 SI-MD-55 M5-AG

Part no.:10.01.06.04196

<https://www.schmalz.com/10.01.06.04196>



FGA 14 SI-MD-55 N016

N° de artículo.:10.01.06.04114

Size: 14

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 1.5

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr