

Inline valve

IV 3 3/2 G1/4-IG G3/8-AG 24V-DC

Part no.:10.05.01.00173

<https://www.schmalz.com/10.05.01.00173>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Inline Valves IV > IV 3 3/2 G1/4-IG G3/8-AG 24V-DC

Inline valve for direct vacuum control at the suction cup



Nominal size: 3 mm


Function: 3/2-way valve

Thread G1: G1/4"-F

Thread G2: G3/8"-M

Voltage DC: 24V - DC

Design Data



Attribute	Value
G1	G1/4"-F
G2	G3/8"-M
G3	M8-M
G4	M5-F
H	51 mm
LG1	9 mm
LG2	9 mm
LG3	6.50 mm
SW1	24 mm

Technical Data

Attribute	Value
Nominal size	3 mm
Control valve	Normally open
Nominal flow rate	20 l/min
Nominal flow rate	1.20 m³/h
Power consumption DC	4.50 W
Voltage DC	24V - DC
Weight	0.07 kg
Product family	IV

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Inline valve

IV 3 3/2 G1/4-IG G3/8-AG 24V-DC

Part no.:10.05.01.00173

<https://www.schmalz.com/10.05.01.00173>

Accessories



ASK B-M8-4 5000 K-4P

Part no.:10.06.02.00031

Electrical connection: Fem connect M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable




ASK WB-M8-4 5000 K-4P

Part no.:10.06.02.00032

Electrical connection: Elbow fem con M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable



VS-V-SA M5-AG

Part no.:10.06.02.00224

Connection: M5-M

Measuring range: -1,00 ... 0,00 bar

Cable length Lk: 3 m

Contact Schmalz

Schmalz S.A.S | Le Prométhée, 65 Avenue Général de Gaulle, 77420 Champs sur Marne, France | +33 1 64 731 730 | schmalz@schmalz.fr

Inline valve

IV 3 3/2 G1/4-IG G3/8-AG 24V-DC

Part no...:10.05.01.00173

<https://www.schmalz.com/10.05.01.00173>



VS-V-SD 60 M5-AG

Part no...:10.06.02.00257

Switching point: - 600

Connection: M5-M

Measuring range: -1,0 ... 0,0 bar

Cable length Lk: 3 m