

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-AG

Part no.:10.01.06.00962

<https://www.schmalz.com/10.01.06.00962>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 9 HT1-60 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/8"-M

Number of folds: 2.5

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
d2	4.10 mm
dn	3.50 mm
Dmax(S)	9.50 mm
Ds	9 mm
G1	G1/8"-M
H	21 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	9
Number of folds	2.50
Connection	G1/8-AG
Curve radius (min) (convex)	10 mm
Volume	0.15 cm ³

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 3
schmalz@schmalz.co.uk

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-AG

Part no.:10.01.06.00962

<https://www.schmalz.com/10.01.06.00962>

Suction force (-600mbar)	0.79 N
Pull-off force	2.30 N
Hose diameter (rec.) d	4 mm
Weight	4.50 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



SPI 9 PEEK

:10.01.06.03280

Size: 9

Material: Polyetheretherketon



SA-NIP N016 G1/8-AG DN350

:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 3
schmalz@schmalz.co.uk

Bellows suction cups (round)

FSG 9 HT1-60 G1/8-AG

Part no.:10.01.06.00962

<https://www.schmalz.com/10.01.06.00962>



FG 9 HT1-60 N016

.:10.01.06.00878

Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 2.5

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 3 from 3
schmalz@schmalz.co.uk