

Suction plate (round)

SGF-HS 350 HT1-60 G1/2-IG

Part no.:10.01.01.13154

<https://www.schmalz.com/10.01.01.13154>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Suction Plates SGF
> SGF-HS 350 HT1-60 G1/2-IG

Flat suction cup (round) for highly dynamic handling of glass



Size: 350


Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Connection: G1/2-IG

Connection: G1/2"-F

Design Data



Attribute	Value
d2	317 mm
d3	170 mm
Dmax(S)	360 mm
Ds	348 mm
G1	G1/2"-F
G2	G1/4"-F
G3	M8-F
H	26.80 mm
L2	76 mm
LG1	14.50 mm
LG2	14.50 mm
LG3	12 mm
W	50 °
X1	45 mm
Y1	120 mm
Z (Stroke)	9 mm
Dmk	58.30 mm
G4	M6-F
LG4	10.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 5
schmalz@schmalz.co.uk

Suction plate (round)

SGF-HS 350 HT1-60 G1/2-IG

Part no...:10.01.01.13154

<https://www.schmalz.com/10.01.01.13154>

Technical Data

Attribute	Value
Suction force (-600mbar)	5700 N
Suction force d2	4730 N
Volume	779.44 cm ³
Curve radius (min) (convex)	3000 mm
Hose diameter (rec.) d	12 mm
Size	350
Number of folds	0
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	2040 g
Product family	SGF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SIEB 27x1 MS-A2 100 100/65

Part no...:10.07.01.00110

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 5
schmalz@schmalz.co.uk

Suction plate (round)

SGF-HS 350 HT1-60 G1/2-IG

Part no...:10.01.01.13154

<https://www.schmalz.com/10.01.01.13154>



TV G1/4-AG 13

Part no...:10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm



PC 350

Part no...:10.01.01.13092

Size: 350



SU 360

Part no...:10.01.01.12842

Size: 360

Clamping range: 360.0 ... 400.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 3 from 5
schmalz@schmalz.co.uk

Suction plate (round)

SGF-HS 350 HT1-60 G1/2-IG

Part no...:10.01.01.13154

<https://www.schmalz.com/10.01.01.13154>



FLK-HD G3/8-AG

Part no...:10.07.06.00235

Thread G1: G3/8"-M

Thread G2: M6-M

Operating temperature: -5 ... 130 °C




FLK-HD G1/4-IG

Part no...:10.07.06.00241

Thread G1: G1/4"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C



FLK-HD G1/2-IG

Part no...:10.07.06.00242

Thread G1: G1/2"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

Spare parts

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 4 from 5
schmalz@schmalz.co.uk

Suction plate (round)

SGF-HS 350 HT1-60 G1/2-IG

Part no...:10.01.01.13154

<https://www.schmalz.com/10.01.01.13154>



VRS-S G1/4-AG

Part no...:10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 5 from 5
schmalz@schmalz.co.uk