

Flat suction cup (round)

PFYN 15 NBR-ESD-55 G1/8-AG

Part no.:10.01.01.14194

<https://www.schmalz.com/10.01.01.14194>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 15 NBR-ESD-55 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 15


Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2 mm
Dmax(S)	17.50 mm
Ds	15 mm
G1	G1/8"-M
H	13 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	1.90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Volume	0.40 cm ³
Curve radius (min) (convex)	12.50 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Flat suction cup (round)

PFYN 15 NBR-ESD-55 G1/8-AG

Part no.:10.01.01.14194

<https://www.schmalz.com/10.01.01.14194>

Weight	4.50 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



PFY 15 NBR-ESD-55 N005

Part no.:10.01.01.13871

Size: 15

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A



SA-NIP N005 G1/8-AG DN200

Part no.:10.01.01.03529

Nipple family: N 005

Thread G1: G1/8"-M

Length L1: 17.5 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in