

Quick change suction cup

SQC-C-RU-80x102-NBR

Part no...:10.01.18.01037

<https://www.schmalz.com/10.01.18.01037>

Home > Vacuum Clamping Technology > Clamping Equipment for Glass Processing > Quick-Change Systems for Bystronic Machines > Schmalz Quick-Change SQC > SQC-C-RU-80x102-NBR

Quick Change Suction Cup



External diameter D: 80 mm

Height H: 102 mm

Construction use: Quick-change system

Dimensions (LxB): Diameter 80 mm


Material: Aluminum

Material: ED

Material hardness [Shore A]: 85 Shore A

Sealing material: Perbunan

Design Data



Attribute	Value
D	80 mm
H	102 mm
H1	119.80 mm

Spare parts

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Quick change suction cup

SQC-C-RU-80x102-NBR

Part no...:10.01.18.01037

<https://www.schmalz.com/10.01.18.01037>



V-RING 63x11 V-070 NBR

Part no...:10.07.08.00554

External diameter D: 75 mm

Type: V-070