

Suction cup (round)

SAUG-SCGS 40 NBR-ESD-55

Part no...:10.01.30.00914

<https://www.schmalz.com/10.01.30.00914>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 40 NBR-ESD-55

Suction cup (round)



Size: 40

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
D1	41 mm
Dmax (N)	25 mm
Dmax(S)	41.50 mm
dn	18.90 mm
Ds	40.50 mm
G1	M20x1-F
H	27.80 mm
LG1	5 mm
Z (Stroke)	3.70 mm

Technical Data

Attribute	Value
Size	40
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	21.20 g
Product family	SAUG-SCGS

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Suction cup (round)

SAUG-SCGS 40 NBR-ESD-55

Part no...:10.01.30.00914

<https://www.schmalz.com/10.01.30.00914>

Spare parts



FLSA 40 NBR-ESD-55

Part no...:10.01.06.04390

Size: 40

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in