

Bellows suction cup (round)

FG 25 HT1-60 N016

Part no.:10.01.06.00883

<https://www.schmalz.com/10.01.06.00883>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 25 HT1-60 N016

Bellows suction cup (round) for very uneven workpieces




Size: 25

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	4.50 mm
d2	10 mm
D1	25 mm
Dk	10 mm
Dmax(S)	26 mm
Ds	23 mm
H	34 mm
H2	3.80 mm
H3	9 mm
Z (Stroke)	18 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	4.71 N
Pull-off force	19 N
Volume	5.22 cm ³
Curve radius (min) (convex)	30 mm
Size	25
Nipple family	N 016
Number of folds	2.50

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Bellows suction cup (round)

FG 25 HT1-60 N016

Part no...:10.01.06.00883

<https://www.schmalz.com/10.01.06.00883>

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	3.90 g
Product family	FG

Accessories



SA-NIP N016 G1/8-AG DN350

Part no...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Bellows suction cup (round)

FG 25 HT1-60 N016

Part no...:10.01.06.00883

<https://www.schmalz.com/10.01.06.00883>



SPI 25 PEEK

Part no...:10.01.06.03286

Size: 25

Material: Polyetheretherketon