

Cup

ISCUP Cup 1 80x80x16

Part no...:10.01.15.00209

<https://www.schmalz.com/10.01.15.00209>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 1 80x80x16

Suction cup for Innospann




Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 16 mm

Design Data



Attribute	Value
B	80 mm
d	60 mm
H	16 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.07 kg

Spare parts

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Cup

ISCUP Cup 1 80x80x16

Part no...:10.01.15.00209

<https://www.schmalz.com/10.01.15.00209>



O-RING 48x2 CR-70

Part no...:10.07.08.00468



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062


Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x81x12 Cup 1 NK-50

Part no...:10.01.15.00020

Width B: 81 mm

Height H: 12 mm

Length L: 81 mm

Suction cup material: Natural rubber NK-50


Type: Cup 1

Cup

ISCUP Cup 1 80x80x16

Part no...:10.01.15.00209

<https://www.schmalz.com/10.01.15.00209>



ISRPL 66x66x8.5

Part no...:10.01.15.00017

Width B: 66 mm

Height H: 8.5 mm

Length L: 66 mm

Type: Cup 1