

Plug union, elbow

STV-W M5-AG 4

Part no...:10.08.02.00155

<https://www.schmalz.com/10.08.02.00155>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W M5-AG 4

Push-in Fitting, swivelling elbow



Thread G1: M5-M


Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 16.4 mm

Design Data



Attribute	Value
d	4 mm
G1	M5-M
dn	2.50 mm
D1	8.50 mm
H	8.70 mm
H1	13.60 mm
L	16.40 mm
L1	21.40 mm
LG1	4.70 mm
SW1	8 mm
SW3	10 mm

Technical Data

Attribute	Value
Hose type	Hose D = 4 d = 2
Hose type	4-2
Material	Nickel plated
Pressure range (operating pressure)	-1.00 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	16 g

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Plug union, elbow

STV-W M5-AG 4


Part no.:10.08.02.00155

<https://www.schmalz.com/10.08.02.00155>

Product family

STV

Accessories



VSL 4-2 PE BL

Part no.:10.07.09.00013

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 4-2 PU MI-TR

Part no.:10.07.09.00001

External diameter D: 4 mm

Internal diameter d: 2 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 20 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 60 °C



VSL 4-2.7 PA MI-TR

Part no.:10.07.09.00063

External diameter D: 4 mm

Internal diameter d: 2.7 mm

Length max.: 50 m

Material hose: PA

Bending radius min.: 30 mm

Pressure range (operating pressure): -0.95 ... 20.00 bar

Operating temperature: -40 ... 90 °C

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in



Plug union, elbow

STV-W M5-AG 4

Part no...:10.08.02.00155

<https://www.schmalz.com/10.08.02.00155>

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in