

Plug union, straight

STVI-GE G1/4-IG 8

Part no.:10.08.02.00154

<https://www.schmalz.com/10.08.02.00154>

Home > Screw in Push Fittings > STVI-GE G1/4-IG 8

Push-in Fitting, straight



Thread G1: G1/4"-F

Hose diameter: 8 mm


Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 14.5 mm

Length L: 33.5 mm

Design Data



Attribute	Value
D	14.50 mm
d	8 mm
G1	G1/4"-F
L	33.50 mm
L2	15 mm
LG1	12 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Brass
Pressure range (operating pressure)	0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	31 g
Product family	STV

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in


Plug union, straight

STVI-GE G1/4-IG 8

Part no.:10.08.02.00154

<https://www.schmalz.com/10.08.02.00154>

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C