

Vacuum hose (meter)

VSL 41-35 PVC-PS GR

Part no.:10.07.09.00010

<https://www.schmalz.com/10.07.09.00010>

Home > Vacuum Lifters and Crane Systems > Vacuum Tube Lifters Jumbo > Spare Parts Vacuum Tube Lifters Jumbo > Spare and Wear Parts Vacuum Tube Lifters JumboErgo / Jumbo Sprint > VSL 41-35 PVC-PS GR

Hose for vacuum and compressed-air systems



External diameter D: 41 mm

Internal diameter d: 35 mm

Length max.: 50 m

Material hose: PVC with PVC-spiral

Bending radius min.: 65 mm

Pressure range (operating pressure): -0.50 ... 0.50 bar

Operating temperature: -20 ... 70 °C

Design Data



Attribute	Value
d	35 mm
D	41 mm

Technical Data

Attribute	Value
Hose type	41-35
Pressure range (operating pressure)	-0.50 ... 0.50 bar
Operating temperature	-20 ... 70 °C
Bending radius min.	65 mm
Length max.	50 m
Weight/Meter	320 g/m
Weight/Meter	0.32 kg/m
Material hose	PVC with PVC-spiral

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Vacuum hose (meter)

VSL 41-35 PVC-PS GR

Part no.:10.07.09.00010

<https://www.schmalz.com/10.07.09.00010>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 35-40 ST-VZ

Part no.:10.07.10.00018

Clamping range: 35.0 ... 40.0 mm

Material: Steel

Surface: galvanised



SSD 37-42 ST-VZ

Part no.:10.07.10.00019

Clamping range: 37.0 ... 42.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in