

Bellows suction cup HT2 (round)

SAB 22 HT2-65 G1/4-AG

Part no.:10.01.06.02420

<https://www.schmalz.com/10.01.06.02420>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 22 HT2-65 G1/4-AG

Bellows suction cup (round) for handling hot workpieces



Size: 22

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A


Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G1/4-AG

Number of folds: 1.5

Design Data



Attribute	Value
dn	3.50 mm
D1	22 mm
Dmax(S)	24 mm
Ds	20.60 mm
G1	G1/4"-M
H	25 mm
LG1	10 mm
SW1	16 mm
Z (Stroke)	5.80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	16 N
Pull-off force	24 N
Lateral force	17 N
Volume	1.50 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	22
Connection	G1/4"-M

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Bellows suction cup HT2 (round)

SAB 22 HT2-65 G1/4-AG

Part no.:10.01.06.02420

<https://www.schmalz.com/10.01.06.02420>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	15.70 g
Number of folds	1.50
Product family	SAB