

Bell suction cup (round)

SAX 30 ED-85 G1/4-AG

Part no.:10.01.19.00213

<https://www.schmalz.com/10.01.19.00213>

Home > Bell-Shaped Suction Cups SAX > SAX 30 ED-85 G1/4-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 30


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: G1/4"-M

Number of folds: 0

Design Data



Attribute	Value
dn	6.10 mm
Dmax(S)	35.20 mm
Ds	31.70 mm
G1	G1/4"-M
H	26 mm
LG1	14.50 mm
SW1	22 mm
Z (Stroke)	4.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	39 N
Lateral force	38 N
Lateral force (oily surface)	41 N
Volume	3.20 cm ³
Curve radius (min) (convex)	18 mm
Size	30
Connection	G1/4"-M
Number of folds	0
Suction cup material	Elastodur ED

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Bell suction cup (round)

SAX 30 ED-85 G1/4-AG

Part no...:10.01.19.00213

<https://www.schmalz.com/10.01.19.00213>

Material hardness [Shore A]	85 Shore A
-----------------------------	------------

Weight	32.50 g
--------	---------

Product family	SAX
----------------	-----
