

Flat suction cup (round)

SGPN 15 NK-40 G1/8-AG

Part no.:10.01.01.10315

<https://www.schmalz.com/10.01.01.10315>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 15 NK-40 G1/8-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 15


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	3.50 mm
Dmax(S)	15.50 mm
Ds	14.50 mm
G1	G1/8"-M
H	16 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	0.90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	5.50 N
Volume	0.28 cm ³
Hose diameter (rec.) d	2 mm
Size	15
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Flat suction cup (round)

SGPN 15 NK-40 G1/8-AG

Part no.:10.01.01.10315

<https://www.schmalz.com/10.01.01.10315>

Weight	4.60 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-AG DN350

Part no.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SGP 15 NK-40 N016

Part no.:10.01.01.10318

Size: 15

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in