

Suction plate (round)

SGF 200 HT1-60 G1/2-IG

Part no.: 10.01.01.12893

<https://www.schmalz.com/10.01.01.12893>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Suction Plates SGF > SGF 200 HT1-60 G1/2-IG

Flat suction cup (round) for highly dynamic handling of glass



Size: 200


Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Connection: G1/2-IG

Connection: G1/2"-F

Design Data



Attribute	Value
d2	185 mm
d3	134 mm
Dmax(S)	213 mm
Ds	206 mm
G1	G1/2"-F
G2	G1/4"-F
H	22 mm
L2	52.80 mm
LG1	14 mm
LG2	14 mm
Z (Stroke)	3.60 mm
Dmk	58.30 mm
G4	M6-F
LG4	10.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1880 N
Suction force d2	1610 N
Volume	144.07 cm ³

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SGF 200 HT1-60 G1/2-IG

Part no...:10.01.01.12893

<https://www.schmalz.com/10.01.01.12893>

Curve radius (min) (convex)	3500 mm
Hose diameter (rec.) d	12 mm
Size	200
Number of folds	0
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	1030 g
Product family	SGF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SIEB 27x1 MS-A2 100 100/65

Part no...:10.07.01.00110



TV G1/4-AG 13

Part no...:10.05.10.00061

Thread G1: G1/4"-M

Thread G2: G1/8"-F

Spring stroke Z: 13 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SGF 200 HT1-60 G1/2-IG

Part no...:10.01.01.12893

<https://www.schmalz.com/10.01.01.12893>



PC 200

Part no...:10.01.01.13089

Size: 200



SU 210

Part no...:10.01.01.12439

Size: 210

Clamping range: 210.0 ... 220.0 mm

Temperature resistance: 80 °C



FLK-HD G3/8-AG

Part no...:10.07.06.00235

Thread G1: G3/8"-M

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SGF 200 HT1-60 G1/2-IG

Part no...:10.01.01.12893

<https://www.schmalz.com/10.01.01.12893>



FLK-HD G1/4-IG

Part no...:10.07.06.00241

Thread G1: G1/4"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C



FLK-HD G1/2-IG

Part no...:10.07.06.00242

Thread G1: G1/2"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

Spare parts



VRS-S G1/4-AG

Part no...:10.08.06.00048

Thread G1: G1/4"-M

Material: Brass

Surface: nickel plated

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction plate (round)

SGF 200 HT1-60 G1/2-IG

Part no...:10.01.01.12893

<https://www.schmalz.com/10.01.01.12893>



DR-SGF 200 HT1-60

Part no...:10.01.01.12891

Size: 200

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Height H: 22 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it