

Flat suction cup (round)

SUF 60 NBR-55 G1/4-IG

Part no.:10.01.01.14062

<https://www.schmalz.com/10.01.01.14062>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 60 NBR-55 G1/4-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 60

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	66.40 mm
Ds	60 mm
dn	5.10 mm
G1	G1/4"-F
H	33.90 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	5.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	140 N
Pull-off force	140 N
Volume	12.70 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	60
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (round)

SUF 60 NBR-55 G1/4-IG

Part no.:10.01.01.14062

<https://www.schmalz.com/10.01.01.14062>

Weight	40.30 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m