

Flat suction cup (round)

SUF 3 NBR-55 SC010

Part no.:10.01.01.14285

<https://www.schmalz.com/10.01.01.14285>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 3 NBR-55 SC010

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 3

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	1.40 mm
Dk	4.20 mm
Dmax(S)	3.70 mm
Ds	3 mm
H	3.50 mm
H2	2 mm
Z (Stroke)	0.30 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	0.30 N
Pull-off force	0.30 N
Volume	0.00 cm ³
Curve radius (min) (convex)	8 mm
Size	3
Nipple family	SC010
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	0 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (round)

SUF 3 NBR-55 SC010

Part no.:10.01.01.14285

<https://www.schmalz.com/10.01.01.14285>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 010 M3-AG

Part no.:10.01.06.04249

Connection geometry: 010

Vacuum connection: M3-M

Fitting length: 2 mm

Nominal diameter dn: 1 mm