

Flat suction cup (oval)

SGO 12x4 NBR-ESD-55 N020

Part no.:10.01.05.00930

<https://www.schmalz.com/10.01.05.00930>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 12x4 NBR-ESD-55 N020


Flat suction cup (oval) for narrow or curved workpieces



Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	5 mm
Bs	4 mm
d	4.20 mm
dn	1.50 mm
Dk	8 mm
Lmax(S)	13 mm
Ls	12 mm
H	15 mm
H2	9.30 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1.80 N
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	0.50 g
Product family	SGO

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (oval)

SGO 12x4 NBR-ESD-55 N020

Part no...:10.01.05.00930

<https://www.schmalz.com/10.01.05.00930>
