

Bellows suction cup HT1 (round)

SAB 50 HT1-60 G1/4-IG

Part no.: 10.01.06.02760

<https://www.schmalz.com/10.01.06.02760>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 50 HT1-60 G1/4-IG

Bellows suction cup (round) for markless handling of workpieces



Size: 50

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Nipple material: Nickel plated

Connection: G1/4-IG

Number of folds: 1.5

Design Data



Attribute	Value
dn	6 mm
D1	39.50 mm
Dmax(S)	56 mm
Ds	50.10 mm
G1	G1/4"-F
H	42 mm
LG1	20 mm
SW1	22 mm
Z (Stroke)	11.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	53 N
Pull-off force	87 N
Lateral force	55 N
Lateral force (oily surface)	52 N
Volume	11.50 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	50

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Bellows suction cup HT1 (round)

SAB 50 HT1-60 G1/4-IG

Part no...:10.01.06.02760

<https://www.schmalz.com/10.01.06.02760>

Number of folds	1.50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	45.20 g
Product family	SAB