

Bellows suction pad (round)

SFB1 15 NBR-ESD-55 SC040

Part no.:10.01.06.04596

<https://www.schmalz.com/10.01.06.04596>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFB1 15 NBR-ESD-55 SC040

Bellows suction cup (round) with 1.5 corr. for dynamic handling workpieces




Size: 15

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
D1	11.50 mm
Dmax(S)	16 mm
Dk	12.80 mm
Ds	15 mm
d	7.50 mm
d1	10.40 mm
d2	4.70 mm
H	16 mm
H2	4.70 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	1 N
Volume	0.76 cm ³
Size	15
Number of folds	1.50
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Curve radius (min) (convex)	12 mm
Nipple family	SC 040

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Bellows suction pad (round)

SFB1 15 NBR-ESD-55 SC040

Part no.:10.01.06.04596

<https://www.schmalz.com/10.01.06.04596>

Product family

SFB1

Accessories



SC 040 M5-AG

Part no.:10.01.06.04346

Connection geometry: 040

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Bellows suction pad (round)

SFB1 15 NBR-ESD-55 SC040

Part no...:10.01.06.04596

<https://www.schmalz.com/10.01.06.04596>
