

Suction cup (round)


SAUG-SCG 30 SI-MD-55 602 B

Part no...:10.01.30.01080

<https://www.schmalz.com/10.01.30.01080>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCG > SAUG-SCG 30 SI-MD-55 602 B

Suction cup (round)



Size: 30


Height H: 26.3 mm

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	39.60 mm
Dmax(S)	32.50 mm
dn	15 mm
Ds	29.50 mm
G1	M37x1-F
H	26.30 mm
LG1	5 mm
Z (Stroke)	5.50 mm

Technical Data

Attribute	Value
Size	30
Pressure range (operating pressure)	bar
Operating temperature	°C
Number of folds	1.50
Weight	16.90 g
Holding force	N
Air consumption	m³/h
Air consumption	l/min

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction cup (round)


SAUG-SCG 30 SI-MD-55 602 B

Part no...:10.01.30.01080

<https://www.schmalz.com/10.01.30.01080>

Material hardness [Shore A]	55 Shore A
Suction rate	m ³ /h
Suction rate	l/min
Suction cup material	Silicone SI metal detectable
Product family	SAUG-SCG

Spare parts



BCG 30 SI-MD-55 SC085

Part no...:10.01.06.04559

Size: 30

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A