

Suction cup (round)


SAUG-SCG 40 SI-MD-55 602 B

Part no...:10.01.30.01081

<https://www.schmalz.com/10.01.30.01081>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCG > SAUG-SCG 40 SI-MD-55 602 B

Suction cup (round)



Size: 40


Height H: 29 mm

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	39.60 mm
Dmax(S)	42 mm
dn	27 mm
Ds	39.40 mm
G1	M37x1-F
H	29 mm
LG1	5 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Size	40
Pressure range (operating pressure)	bar
Operating temperature	°C
Number of folds	1.50
Weight	19.70 g
Holding force	N
Air consumption	m³/h
Air consumption	l/min

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Suction cup (round)


SAUG-SCG 40 SI-MD-55 602 B

Part no...:10.01.30.01081

<https://www.schmalz.com/10.01.30.01081>

Material hardness [Shore A]	55 Shore A
Suction rate	m ³ /h
Suction rate	l/min
Suction cup material	Silicone SI metal detectable
Product family	SAUG-SCG

Spare parts



BCG 40 SI-MD-55 SC095

Part no...:10.01.06.04560

Size: 40

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A