

Basic Ejector

SBP 07 G01 SDA

Part no.:10.02.01.00600

<https://www.schmalz.com/10.02.01.00600>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP > SBP 07 G01 SDA

Basic ejector for universal use



Nozzle diameter: 0.7 mm

Add. function: Axial silencer

Degree of evacuation: 85 %


Connection: M5(1)-M5(2)

Pressure optimal: 4.5 bar

Suction rate (max.): 16 l/min

Air consumption suction: 22 l/min

Design Data



Attribute	Value
B	10 mm
d	4.20 mm
D	9 mm
G1	M5-F
G2	M5-F
H	26 mm
H1	31 mm
H2	5.20 mm
H3	12 mm
L	45 mm
L1	74 mm
L2	18 mm
L3	5 mm
L4	12.50 mm
LG1	5 mm
LG2	5 mm
SW1	8 mm
SW2	8 mm
X1	20 mm

Technical Data

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Basic Ejector

SBP 07 G01 SDA

Part no.:10.02.01.00600

<https://www.schmalz.com/10.02.01.00600>

Attribute	Value
Nozzle diameter	0.70 mm
Degree of evacuation	85 %
Suction rate (max.)	1 m ³ /h
Suction rate (max.)	16 l/min
Air consumption suction	1.30 m ³ /h
Air consumption suction	22 l/min
Sound level free	65 dB(A)
Sound level suction	59 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar
Pressure optimal	4.50 bar
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	2 mm
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	43.5 ... 87.0
Suction rate (max.)	0.57 cfm
Air consumption suction	0.78 cfm
Weight	7.50 g
Product family	SBP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



BEF-PL 110x44.5x3 SBP

Part no.:10.02.01.00511

Length L: 110 mm

Width B: 44.5 mm

Height H: 3 mm

Construction use: Basic ejector SBP

Basic Ejector

SBP 07 G01 SDA

Part no...:10.02.01.00600

<https://www.schmalz.com/10.02.01.00600>



SET SBP M4-IG

Part no...:10.02.01.00769

Length L: 50 mm

Width B: 14 mm

Construction use: Basic ejector SBP

Type: M4-IG



VFI CN6/4 50

Part no...:10.07.01.00241

Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm



VFI 4/2 50

Part no...:10.07.01.00329

Connection: Hose 4/2

Filter pore size: 50 µm

Spare parts

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Basic Ejector

SBP 07 G01 SDA

Part no...:10.02.01.00600

<https://www.schmalz.com/10.02.01.00600>



SD M5-AG 9x24

Part no...:10.02.01.00539

Thread G1: M5-M

External diameter D: 9 mm

Length L: 24 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it