

Compact ejector

SCP 30 FS RP

Part no...:10.02.02.01643

<https://www.schmalz.com/10.02.02.01643>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Compact Ejectors > Compact Ejectors SCP-FS > SCP 30 FS RP

Compact ejector with integrated functions



Nozzle diameter: 3 mm
Suction rate (max.): 200 l/min
Air consumption suction: 420 l/min
Pressure range (operating pressure): 5.0 ... 6.0 bar
Control valve: External control
Function: pneumatic air-saving function

Design Data



Attribute	Value
B	25 mm
d	5.50 mm
G1	G1/4"-F
G2	G3/8"-F
H	77 mm
H1	150.50 mm
H2	73.50 mm
H3	20.10 mm
L	112.50 mm
L2	37.50 mm
X1	49.50 mm
X2	69.50 mm
Y1	12 mm

Technical Data

Attribute	Value
Nozzle diameter	3 mm
Degree of evacuation	85 %
Suction rate (max.)	200 l/min
Control valve	External control



Compact ejector

SCP 30 FS RP

Part no...:10.02.02.01643

<https://www.schmalz.com/10.02.02.01643>

Suction rate (max.)	7.06 cfm
Product family	SCP

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it