

Vacuum blower

SB 1050 290 11 IE3-TYP3

Part no.:10.04.01.00085

<https://www.schmalz.com/10.04.01.00085>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB > SB 1050 290 11 IE3-TYP3

Vacuum Blower for high suction rate



Suction rate (50 Hz): 1,050 m³/h

Suction rate (60 Hz): 1,250 m³/h

Vacuum (50 Hz): 290 mbar

Vacuum (60 Hz): 270 mbar

Rated power 50 Hz: 11 kW

Rated power 60 Hz: 13.2 kW

Voltage at 50Hz: D200V/Y350V ±10 %


Voltage at 60Hz: D220V/Y380-400V ±10%

Construction: IE3:JPN/KOR/BRA

Permission: IE3

Weight: 125 kg

Design Data



Attribute	Value
B	525 mm
B1	563 mm
D2	100 mm
G1	G4"-F
G5	M8-F
H	611 mm
L	643 mm
X1	350 mm
Y1	400 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	1050 m³/h
Suction rate (50 Hz)	17,499.90 l/min
Suction rate (60 Hz)	1250 m³/h
Vacuum (50 Hz)	290 mbar
Vacuum (60 Hz)	270 mbar
Protection type IP	IP 55

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum blower

SB 1050 290 11 IE3-TYP3

Part no.:10.04.01.00085

<https://www.schmalz.com/10.04.01.00085>

Rated power 50 Hz	11 kW
Rated power 60 Hz	13.20 kW
Voltage at 50Hz	D200V/Y350V ±10 %
Voltage at 60Hz	D220V/Y380-400V ±10%
Sound level at 50 Hz	75 dB(A)
Noise level (60 Hz)	79 dB(A)
Weight	125 kg
Construction	IE3-TYP3
Construction	IE3:JPN/KOR/BRA
Product family	SB

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



SBB-230V-AC-ST-VZ-LUE SB

Part no.:10.04.04.00239

Construction use: Blower SB

Voltage DC: 230V - AC

Material: Steel

Length L: 1,055 mm

Width B: 727 mm

Height H: 703 mm



SBB-24V-DC-ST-VZ-LUE SB

Part no.:10.04.04.00318

Construction use: Blower SB

Voltage DC: 24V - DC

Material: Steel

Length L: 1,055 mm

Width B: 727 mm

Height H: 703 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum blower

SB 1050 290 11 IE3-TYP3

Part no...:10.04.01.00085

<https://www.schmalz.com/10.04.01.00085>



STF 100 P 24.0 SSB

Part no...:10.07.01.00401

Connection: Ø100mm

Shape: Piclon housing

Nominal flow rate: 1,440 m³/h

Filter pore size: 3 µm

Additional function: Hose clamps SSB



SD SB FITTING SD

Part no...:10.04.04.00363

Construction use: Blower SB

and: Silencer