

Plug union, elbow

STV-W M5-AG 6

Part no.:10.08.02.00296

<https://www.schmalz.com/10.08.02.00296>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W M5-AG 6

Push-in Fitting, swivelling elbow




Pressure range (operating pressure): bar

Length L: 20.8 mm

Height H: 13 mm

Thread G1: M5-M

Design Data



Attribute	Value
d	6 mm
D1	11.50 mm
dn	4 mm
G1	M5-M
H	13 mm
H1	16.50 mm
L	20.80 mm
L1	25.50 mm
LG1	4 mm
SW1	8 mm
SW3	8 mm

Technical Data

Attribute	Value
Weight	4.30 g

Accessories

Contact Schmalz


Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Plug union, elbow

STV-W M5-AG 6

Part no.:10.08.02.00296

<https://www.schmalz.com/10.08.02.00296>



VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C