

Flat suction cup (oval)

SGO 75x25 HT1-60 N023

Part no.:10.01.05.00441

<https://www.schmalz.com/10.01.05.00441>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 75x25 HT1-60 N023

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 75 x 25

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Design Data



Attribute	Value
Bmax(S)	27.50 mm
Bs	24 mm
d	11.50 mm
d1	13 mm
dn	4 mm
Dk	17.50 mm
Lmax(S)	77 mm
Ls	74 mm
H	21 mm
H2	8 mm
H3	10 mm
Z (Stroke)	2.80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	78.30 N
Dimensions (LxB)	75 x 25
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	17.80 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (oval)

SGO 75x25 HT1-60 N023

Part no...:10.01.05.00441

<https://www.schmalz.com/10.01.05.00441>

Product family

SGO

Accessories



SA-NIP N023 G1/4-AG DN350

Part no...:10.01.05.00122

Thread G1: G1/4"-M

Length L1: 25 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N023 G1/4-IG DN350

Part no...:10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it