

## Bellows suction cup f SCG(S)-gripper

BCG 20 NBR-ESD-55 SC085

Part no...:10.01.06.04573

<https://www.schmalz.com/10.01.06.04573>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > BCG 20 NBR-ESD-55 SC085

### Bellows suction cup (round) for high volumeflow with optimum adaption to uneven surfaces




Size: 20

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d2         | 15.50 mm |
| Dmax(S)    | 25 mm    |
| Ds         | 21.50 mm |
| H          | 13 mm    |
| Z (Stroke) | 3 mm     |

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction cup material        | Nitrile rubber NBR-ESD |
| Material hardness [Shore A] | 55 Shore A             |
| Weight                      | 2 g                    |

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)