

Bellows suction cup f SCG(S)-gripper

BCG 40 NBR-ESD-55 SC095

Part no...:10.01.06.04575

<https://www.schmalz.com/10.01.06.04575>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > BCG 40 NBR-ESD-55 SC095

Bellows suction cup (round) for high volumeflow with optimum adaption to uneven surfaces




Size: 40

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d2	26 mm
Dmax(S)	42 mm
Ds	39.40 mm
H	19.50 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Weight	8 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it