

Vacuum filter (inline)

VFI 4/2 50

Part no...:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Inline Filters VFI > VFI 4/2 50


Vacuum filter with replaceable filter cartridge



Connection: Hose 4/2

Filter pore size: 50 µm

Design Data



Attribute	Value
d	4 mm
D	17 mm
L	55 mm

Technical Data

Attribute	Value
Connection	Hose 4/2
Filter pore size	50 µm
Nominal flow rate	32 l/min
Nominal flow rate	1.92 m³/h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Weight	6.30 g
Product family	VFI

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Vacuum filter (inline)

VFI 4/2 50

Part no.:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

Accessories



FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)

Spare parts



FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)