

## Flexolink HD

FLK-HD G1/4-IG

Part no.: 10.07.06.00241

<https://www.schmalz.com/10.07.06.00241>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > FLK-HD G1/4-IG

### Flexible, reinforced suction cup mounting FLK-HD for adaption to sloping surfaces




Thread G1: G1/4"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

### Design Data



| Attribute      | Value    |
|----------------|----------|
| L              | 31.60 mm |
| D              | 69 mm    |
| dn             | 9 mm     |
| d              | 6.40 mm  |
| G1             | G1/4"-F  |
| LG1            | 12 mm    |
| G2             | M6-M     |
| LG2            | 10.50 mm |
| SW1            | 17 mm    |
| SW2            | 5 mm     |
| Dmk            | 58.30 mm |
| W              | 7.50 °   |
| Fitting length | 31.60 mm |

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)