

Hose sleeve

ST G1/8-AG 4 MS-ROH

Part no.:10.08.03.00153

<https://www.schmalz.com/10.08.03.00153>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/8-AG 4 MS-ROH

Hose sleeve



Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm


Material: Brass

Surface: raw

Length L: 4 mm

Nominal diameter dn: 2.5 mm

Design Data



Attribute	Value
dn	2.50 mm
D	3.90 mm
G1	G1/8"-M
L	4 mm
L1	28 mm
LG1	7 mm
SW1	14 mm

Technical Data

Attribute	Value
Material	Brass
Weight	7 g

Accessories

Contact Schmalz


Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Hose sleeve

ST G1/8-AG 4 MS-ROH

Part no...:10.08.03.00153

<https://www.schmalz.com/10.08.03.00153>



VSL 6-4 PE BL

Part no...:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no...:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no...:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it