

## Hose sleeve

ST G1/8-AG 6 MS-V

Part no.:10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/8-AG 6 MS-V

### Hose sleeve



Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm


Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4.4 mm

### Design Data



| Attribute | Value   |
|-----------|---------|
| dn        | 4.40 mm |
| D         | 5.40 mm |
| G1        | G1/8"-M |
| L         | 5 mm    |
| L1        | 34 mm   |
| LG1       | 8 mm    |
| SW1       | 14 mm   |

### Technical Data

| Attribute | Value |
|-----------|-------|
| Material  | Brass |
| Weight    | 13 g  |

### Accessories

#### Contact Schmalz


Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Hose sleeve

ST G1/8-AG 6 MS-V

Part no...:10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>



### VSL 6-4 PE BL

Part no...:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



### VSL 6-4 PTFE MI-TR

Part no...:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



### VSL 6-4 PU MI-TR

Part no...:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

## Contact Schmalz


Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Hose sleeve

ST G1/8-AG 6 MS-V

Part no.:10.08.03.00154

<https://www.schmalz.com/10.08.03.00154>



### VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



### VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C