

Quick change module RMQC

RMQC 50 UNI IOL LED M12-5 MATCH

Part no...:10.08.09.00007

<https://www.schmalz.com/10.08.09.00007>

Home > Vacuum Technology for Robotics > End-of-Arm Ecosystem MATCH > Quick-Change Module RMQC > RMQC 50 UNI IOL LED M12-5 MATCH

Quick-change module for easy and fast connection of EoA grippers of the MATCH series



Pitch diameter D mk: 50 mm

for: Universal

Type: ISO TK 50


Inputs/outputs: IO-Link

Type: LED-Band

Electrical connection: Male connect M12, 5 pol

Construction: Quick-change system MATCH

Design Data



Attribute	Value
D	75 mm
d	6.40 mm
D2	31.50 mm
Dmk	50 mm
G1	M12-M
G2	M7-F
G3	M3-F
G4	M4-F
H	28 mm
H1	31 mm
Lk	190 mm

Technical Data

Attribute	Value
Construction	Quick-change system MATCH
for	Universal
Type	ISO TK 50
Type	LED-Band
Shape mounting elements	Fluid channel closed
Number of load cycles	100000
Inputs/outputs	IO-Link

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Quick change module RMQC

RMQC 50 UNI IOL LED M12-5 MATCH

Part no.:10.08.09.00007

<https://www.schmalz.com/10.08.09.00007>

Electrical connection	M12-5
Force axial (max)	500 N
Moment (Y)	40 Nm
Axle offset max	1 mm
Tightening force	50 N
Dissolving power	0 N
with	E-transfer electr / pneum
Operating temperature	5 ... 60 °C
Weight	300 g

Accessories



VENT-BGR EMVP-5 3/2 NC 24V-DC

Part no.:10.08.09.00032

Voltage DC: 24V - DC

Pressure range (operating pressure): -0.9 ... 8.0 bar

Control valve: Normally closed

Nominal size: 5 mm

Nominal flow rate: 3 m³/h

Type: RECB