

Plug union, T

STV-T G1/4-AG 8

Part no.: 10.09.02.00043

<https://www.schmalz.com/10.09.02.00043>

Home > Screw in Push Fittings > STV-T G1/4-AG 8

Push-in Fitting, T



Thread G1: G1/4"-M


Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48.5 mm

Design Data



Attribute	Value
d	8 mm
G1	G1/4"-M
dn	6.50 mm
D1	14.10 mm
H	16.10 mm
H1	23.20 mm
L	48.50 mm
LG1	7.60 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	59.30 g
Product family	STV

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Plug union, T

STV-T G1/4-AG 8

Part no.:10.09.02.00043

<https://www.schmalz.com/10.09.02.00043>

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it