

Needle gripper


SNG-DL 1.2 24

Part no.:10.01.29.00011

<https://www.schmalz.com/10.01.29.00011>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Needle Grippers > Needle Grippers SNG-DL > SNG-DL 1.2 24

Needle gripper "SNG-DL", particularly large and robust version




Number of needles: 24

Needle diameter: 1.2 mm

Needle stroke Z(NA): 17.5 mm

Pressure range (operating pressure): 3.0 ... 10.0 bar

Design Data



Attribute	Value
B	55 mm
G1	M5-F
G4	M4-F
H	117 mm
L	263.50 mm
X1	20 mm
Y1	20 mm

Technical Data

Attribute	Value
Number of needles	24
Needle diameter	1.20 mm
Pressure range (operating pressure)	3.0 ... 10.0 bar
Operating temperature	5 ... 60 °C
Installation position	BEL
Weight	1500 g

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it


Needle gripper

SNG-DL 1.2 24

Part no.:10.01.29.00011

<https://www.schmalz.com/10.01.29.00011>

Accessories



BEF-PL 31x34x11.5 G1/4-IG SNG

Part no.:10.01.29.00093

Construction use: Needle gripper

Length L: 31 mm

Width B: 34 mm

Height H: 11.5 mm

Thread G1: G1/4"-F



STV-GE M5-AG 6

Part no.:10.08.02.00201

Thread G1: M5-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 9.9 mm

Length L: 18.8 mm



STV-W M5-AG 6

Part no.:10.08.02.00296

Pressure range (operating pressure): bar

Length L: 20.8 mm

Height H: 13 mm

Thread G1: M5-M

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Needle gripper

SNG-DL 1.2 24

Part no.:10.01.29.00011

<https://www.schmalz.com/10.01.29.00011>



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m


Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Spare parts



ERS SNG-DL 1.2

Part no.:10.01.29.00102

Construction use: Needle gripper

Size: DL

contains: 2 needle wedges mounted

Needle diameter: 1.2 mm