

## Tooling-System-Schmalz-Ejektor


SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Decentralized Ejectors > Ejectors With Blow Off  
System SEAC RP > SEAC 10 RP VS-T L

### Tooling-System-Schmalz-Ejektor



Nozzle diameter: 1 mm


Function: pneumatic air-saving function

Add. function: electronic vacuum switch

construction shape compact ejectors: Version left

Pressure range (operating pressure): 4.0 ... 6.0 bar

### Design Data



| Attribute | Value    |
|-----------|----------|
| B         | 44.50 mm |
| B3        | 14.20 mm |
| d         | 4.30 mm  |
| d1        | 13.80 mm |
| D         | 27 mm    |
| G1        | G1/8"-F  |
| G3        | M8-M     |
| G4        | G1/8"-F  |
| H         | 38.30 mm |
| H1        | 39.80 mm |
| H2        | 29.30 mm |
| L         | 52 mm    |
| L1        | 88.10 mm |
| L2        | 29.50 mm |
| L3        | 8 mm     |
| L4        | 22 mm    |
| X1        | 28 mm    |

### Technical Data

| Attribute | Value |
|-----------|-------|
|-----------|-------|

#### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>

|                                     |                 |
|-------------------------------------|-----------------|
| Nozzle diameter                     | 1 mm            |
| Degree of evacuation                | 85 %            |
| Suction rate (max.)                 | 36 l/min        |
| Suction rate (max.)                 | 2.10 m³/h       |
| Air consumption suction             | 65 l/min        |
| Air consumption suction             | 3.90 m³/h       |
| Max. air consumption blow off       | 92 l/min        |
| Pressure range (operating pressure) | 4.0 ... 6.0 bar |
| Weight                              | 180 g           |
| Pressure range (operating pressure) | 58.0 ... 87.0   |
| Suction rate (max.)                 | 1.27 cfm        |
| Air consumption suction             | 2.30 cfm        |
| Air consumption blow off            | 3.18 cfm        |
| Max. vacuum                         | 25.10 inHg      |
| Product family                      | SEAC-RP         |

Note: Air consumption: At optimal operating pressure (4,5 bar)

### Accessories



#### ASK B-M8-4 5000 K-4P

Part no...:10.06.02.00031

Electrical connection: Fem connect M8, 4 pol

Cable length: 5,000 mm

Material hose: PUR cable

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>



**ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-S**

Part no...:10.02.02.03483

Length L: 45.5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



**ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-L**

Part no...:10.02.02.03484

Length L: 45.5 mm

Width B: 21 mm

Height H: 44 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC



**ADP-EJ 38x20x11-G1/4-IG SEAC**

Part no...:10.02.02.04067

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/4"-F

Construction use: Compact ejectors SEAC

## Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T L

Part no...:10.02.02.03297

<https://www.schmalz.com/10.02.02.03297>



**ADP-EJ 38x20x11-G1/8-IG SEAC**

Part no...:10.02.02.04068

Length L: 38 mm

Width B: 20 mm

Height H: 11 mm

Thread G1: G1/8"-F

Construction use: Compact ejectors SEAC

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)