

## Robots-Set ECBPMi

### ROB-SET ECBPMi FRUITCORE

Part no...:10.03.01.00677

<https://www.schmalz.com/10.03.01.00677>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Generators End-of-Arm > Handling Sets  
ECBPMi > ROB-SET ECBPMi FRUITCORE

### Complete set for connecting and integrating the CobotPump ECBPMi to lightweight robots



for: EMPTY VALUE


Type: HORST

contains: Suction cup

and: Screws

Degree of evacuation: 60 %

### Design Data



| Attribute | Value    |
|-----------|----------|
| Lk        | 300 mm   |
| D         | 68 mm    |
| D2        | 62.70 mm |
| D mk1     | 46 mm    |
| D mk2     | 62.70 mm |
| G1        | M4-F     |
| G2        | G1/4"-F  |
| G3        | M4-F     |
| G4        | M8-M     |
| L         | 73.40 mm |
| L1        | 76.40 mm |
| LG1       | 6 mm     |
| LG2       | 11.50 mm |

### Technical Data

| Attribute            | Value      |
|----------------------|------------|
| Suction rate (max.)  | 1.60 l/min |
| Degree of evacuation | 60 %       |
| Voltage DC           | 24V - DC   |
| Rated power          | 7.20 W     |

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Robots-Set ECBPMi

ROB-SET ECBPMi FRUITCORE

Part no.:10.03.01.00677

<https://www.schmalz.com/10.03.01.00677>

|                       |                         |
|-----------------------|-------------------------|
| Rated current         | 0.30 A                  |
| Electrical connection | Male connect M8, 4 pole |
| Operating temperature | 0 ... 40 °C             |
| Protection type IP    | IP 40                   |
| for                   | EMPTY VALUE             |
| Product family        | ROB-SET-ECBPM           |

### Accessories



#### SLG FSGA 2 102x57

Part no.:10.01.10.14043

Length L: 102 mm

Width B: 57 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 2



#### SLG FSGA 3 102x102

Part no.:10.01.10.14042

Length L: 102 mm

Width B: 102 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 3

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Robots-Set ECBPMi

ROB-SET ECBPMi FRUITCORE

Part no...:10.03.01.00677

<https://www.schmalz.com/10.03.01.00677>



### SLG FSGA 4 102x75.3

Part no...:10.01.10.14041

Length L: 102 mm

Width B: 75.3 mm

Height H: 57 mm

Suction cup typ: FSGA

Number of suction cells: 4

## Spare parts



### ECBPMi 24V-DC FK

Part no...:10.03.01.00500

Voltage DC: 24V - DC

Rated current: 0.3 A

Electrical connection: Spring contact

Operating temperature: 0 ... 40 °C

Suction rate (max.): 1.6 l/min

Rated power: 7.2 W



### SPB1 30 ED-65 G1/4-AG

Part no...:10.01.06.04530

Size: 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 1.5

## Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)

## Robots-Set ECBPMi

ROB-SET ECBPMi FRUITCORE

Part no...:10.03.01.00677

<https://www.schmalz.com/10.03.01.00677>



### SFF 20 SI-55 G1/4-AG

Part no...:10.01.01.14621

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

### Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | [schmalz@schmalz.it](mailto:schmalz@schmalz.it)