

Flexolink HD

FLK-HD G1/4-IG

Part no.: 10.07.06.00241

<https://www.schmalz.com/10.07.06.00241>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > FLK-HD G1/4-IG

Flexible, reinforced suction cup mounting FLK-HD for adaption to sloping surfaces




Thread G1: G1/4"-F

Thread G2: M6-M

Operating temperature: -5 ... 130 °C

Design Data



Attribute	Value
L	31.60 mm
D	69 mm
dn	9 mm
d	6.40 mm
G1	G1/4"-F
LG1	12 mm
G2	M6-M
LG2	10.50 mm
SW1	17 mm
SW2	5 mm
Dmk	58.30 mm
W	7.50 °
Fitting length	31.60 mm

Contact Schmalz

Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it