

Flat suction cup (round)


PFG 30 PU-55 N007

Part no.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 30 PU-55 N007

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 30

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	6 mm
d1	11 mm
Dk	15.10 mm
Dmax(S)	31.50 mm
Ds	28.80 mm
H	12 mm
H2	7 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	34 N
Volume	1.56 cm ³
Curve radius (min) (convex)	40 mm
Size	30
Nipple family	N 007
Suction cup material	Polyurethane PU
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624031
schmalz@schmalz.co.kr

Flat suction cup (round)

PFG 30 PU-55 N007

Part no.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>

Weight	3 g
Product family	PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N007 G1/8-AG DN240

Part no.:10.01.01.03531

Nipple family: N 007
Thread G1: G1/8"-M
Length L1: 21 mm
Length L: 5 mm
Fitting length: 5 mm
Nominal diameter dn: 2.4 mm
Material: Aluminum
Spanner size SW2: 4 mm



SA-NIP N007 G1/8-IG DN350

Part no.:10.01.01.03523

Nipple family: N 007
Thread G1: G1/8"-F
Length L1: 24.5 mm
Length L: 16 mm
Fitting length: 16 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum
Spanner size SW2: 4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Flat suction cup (round)

PFG 30 PU-55 N007

Part no.:10.01.01.00054

<https://www.schmalz.com/10.01.01.00054>



SU 30

Part no.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624311
schmalz@schmalz.co.kr