

Flat suction cup (round) sensitive

SGN 8 NBR-55 M5-AG

Part no.:10.01.01.00715

<https://www.schmalz.com/10.01.01.00715>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > Flat Suction Cups SGN > SGN 8 NBR-55 M5-AG

Flat suction cup (round), handling sensitive workpieces with uneven surfaces



Size: 8


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M5-AG

Design Data



Attribute	Value
Dmax(S)	9 mm
dn	1 mm
Ds	8 mm
G1	M5-M
H	11.50 mm
LG1	4.50 mm
SW1	8 mm
Z (Stroke)	1.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	8
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	2.30 N
Material hardness [Shore A]	55 Shore A

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flat suction cup (round) sensitive

SGN 8 NBR-55 M5-AG

Part no.:10.01.01.00715

<https://www.schmalz.com/10.01.01.00715>

approx. 2 m

Spare parts



SA-NIP N040 M5-AG DN100

Part no.:10.01.01.00714

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum



SG 8 NBR-55 N040

Part no.:10.01.01.00713

Size: 8

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 8.5 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr