

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Spring Plungers > Spring Plungers
FSTE-HDB > FSTE-HDB G3/8-AG 25 VG-AB

Spring plunger with damping and height compensation, heavy-duty and ball guided anti-rotation guard




Suction cup connection: G3/8"-M

Vacuum connection: G1/8"-F

Spring stroke Z: 25 mm

Shape mounting elements: with anti-rotation guard anti-block

Design Data



Attribute	Value
G1	G1/8"-F
G2	G3/8"-M
G3	M20x1.5-M
H	118.80 mm
H2	35.30 mm
LG1	12 mm
LG2	8 mm
LG3	44 mm
SW1	24 mm
SW2	17 mm
SW3	22 mm
Z (Stroke)	25 mm

Recommendation: Avoid maximum plunger stroke Z during continuous operation to extend service life Ensure that the hose guide is free from distortion

Technical Data

Attribute	Value
Shape mounting elements	with anti-rotation guard anti-block
Spring rate	0.71 N/mm
Spring pretension	3.06 N

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>

Spring force, center	11.95 N
Vertical load	2400 N
Horizontal load	747 N
Weight	240 g
Operating temperature	0 ... 80 °C
Product family	FSTE-HDB

Note: Spring force: Referred to 50 % of operating stroke Vertical load: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position.

Accessories



RED-STK G1/2-AG G3/8-IG MS-V

Part no.:10.08.04.00096

Thread G1: G1/2"-M

Thread G2: G3/8"-F

Material: Brass

Surface: nickel plated

Length L: 6 mm



HTR-STA 55 1N D20 WI

Part no.:10.08.03.00086

Length L: 55 mm

Connection 1: Sliding block

Connection of suction cup, spring plunger: Contour D20-G1/4

Shape: angled

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



HTR-UNI 2N FSTE-HDB

Part no.:10.01.03.00332

Operating temperature: °C

Shape: for FSTE-HDB

Cross-beam connection: 2 T-slots



ST G1/8-AG 4 MS-ROH

Part no.:10.08.03.00153

Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: raw

Length L: 4 mm

Nominal diameter dn: 2.5 mm



ST G1/8-AG 6 MS-V

Part no.:10.08.03.00154

Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4.4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624831
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



ST G1/8-AG 9 MS-V

Part no.:10.08.03.00155

Thread G1: G1/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4 mm



STV-GE G1/8-AG 4

Part no.:10.08.02.00202

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 7.9 mm

Length L: 13.7 mm



STV-GE G1/8-AG 6

Part no.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



STV-GE G1/8-AG 8

Part no.:10.08.02.00206

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20.7 mm



STV-W G1/8-AG 4

Part no.:10.08.02.00156

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 16.4 mm



STV-W G1/8-AG 6

Part no.:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20.1 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624531
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



STV-W G1/8-AG 8

Part no.:10.08.02.00160

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm



STV-GE G1/8-AG 6 HT

Part no.:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11.6 mm

Length L: 19 mm



STV-W G1/8-AG 6

Part no.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20.8 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



STV-W G1/8-AG 6 HT

Part no.:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22.5 mm



STV-WF G1/8-AG 4

Part no.:10.08.02.00166

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 17.4 mm



STV-WF G1/8-AG 6

Part no.:10.08.02.00168

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 21.4 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



STV-WF G1/8-AG 8

Part no.:10.08.02.00170

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 23.4 mm



STV-WF G1/8-AG 10

Part no.:10.08.02.00257

Thread G1: G1/8"-M

Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25.2 mm



STV-T G1/8-AG 4

Part no.:10.09.02.00039

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 32.5 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624831
schmalz@schmalz.co.kr

Spring plungers

FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

<https://www.schmalz.com/10.01.02.01436>



STV-T G1/8-AG 6

Part no.:10.09.02.00040

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41.5 mm



STV-T G1/8-AG 8

Part no.:10.09.02.00041

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48.7 mm

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 85624931
schmalz@schmalz.co.kr