

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Part no.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 30x10 SI-HD-65 G1/8-IG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: G1/8"-F

Design Data



Attribute	Value
Bmax(S)	11.50 mm
Bs	9.40 mm
dn	2.50 mm
G1	G1/8"-F
H	25 mm
LG1	9 mm
Lmax(S)	30.50 mm
Ls	29.40 mm
SW1	14 mm
Z (Stroke)	1.50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	12.20 N
Volume	0.52 cm ³
Curve radius (min) (convex)	7.50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Part no.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>

Weight	7.50 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SGO 30x10 SI-HD-65 N022

Part no.:10.01.05.01037

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N022 G1/8-IG DN350

Part no.:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 13 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Part no.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>



ZOKL 11-13

Part no.:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624311
schmalz@schmalz.co.kr