

Flat suction cup (oval)

SGON 60x20 SI-HD-65 G1/4-AG

Part no.:10.01.05.01058

<https://www.schmalz.com/10.01.05.01058>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 60x20 SI-HD-65 G1/4-AG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: G1/4"-M

Design Data



Attribute	Value
Bmax(S)	22 mm
Bs	19 mm
dn	3.50 mm
G1	G1/4"-M
H	26 mm
LG1	10 mm
Lmax(S)	61 mm
Ls	59 mm
SW1	17 mm
Z (Stroke)	2.50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	50.10 N
Volume	3.61 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	6 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 60x20 SI-HD-65 G1/4-AG

Part no.:10.01.05.01058

<https://www.schmalz.com/10.01.05.01058>

Weight	19 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SGO 60x20 SI-HD-65 N023

Part no.:10.01.05.01039

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N023 G1/4-AG DN350

Part no.:10.01.05.00122

Thread G1: G1/4"-M

Length L1: 25 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031
schmalz@schmalz.co.kr

Flat suction cup (oval)

SGON 60x20 SI-HD-65 G1/4-AG

Part no.:10.01.05.01058

<https://www.schmalz.com/10.01.05.01058>



SA-NIP N023 G1/4-IG DN350

부품 번호:10.01.05.00121

Thread G1: G1/4"-F

Length L1: 25 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



ZOKL 15-18

부품 번호:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8762431
schmalz@schmalz.co.kr