

## Bellows suction cups (round)

FSG 9 SI-55 M5-AG

Part no.:10.01.06.00037

<https://www.schmalz.com/10.01.06.00037>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 9 SI-55 M5-AG

### Bellows suction cup (round) for very uneven workpieces



Size: 9

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2.5

Vacuum connection: M5-M

### Design Data



| Attribute  | Value   |
|------------|---------|
| d2         | 4.10 mm |
| dn         | 2.50 mm |
| Dmax(S)    | 9.50 mm |
| Ds         | 9 mm    |
| G1         | M5-M    |
| H          | 20 mm   |
| LG1        | 5 mm    |
| SW1        | 7 mm    |
| Z (Stroke) | 3 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                |
|-----------------------------|----------------------|
| Suction cup material        | Silicone SI          |
| Material hardness [Shore A] | 55 Shore A           |
| Size                        | 9                    |
| Number of folds             | 2.50                 |
| Connection                  | M5-AG                |
| Curve radius (min) (convex) | 10 mm                |
| Volume                      | 0.15 cm <sup>3</sup> |

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 81624031  
schmalz@schmalz.co.kr

## Bellows suction cups (round)

FSG 9 SI-55 M5-AG

Part no.:10.01.06.00037

<https://www.schmalz.com/10.01.06.00037>

|                          |        |
|--------------------------|--------|
| Suction force (-600mbar) | 0.79 N |
| Pull-off force           | 2.30 N |
| Hose diameter (rec.) d   | 2 mm   |
| Weight                   | 1.80 g |
| Product family           | FSG    |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SPI 9 PEEK

Part no.:10.01.06.03280

Size: 9

Material: Polyetheretherketon

### Spare parts



#### SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031  
schmalz@schmalz.co.kr

## Bellows suction cups (round)

FSG 9 SI-55 M5-AG

Part no.:10.01.06.00037

<https://www.schmalz.com/10.01.06.00037>



### FG 9 SI-55 N016

Part no.:10.01.06.00056

Size: 9

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2.5

### Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8624311  
schmalz@schmalz.co.kr